

DW-HD-621-M8-100 Cut Sheet



Contrinex inductive proximity sensor, tubular, 8mm diameter x 60mm body, 304 stainless steel housing, NPN, N.O., 2mm sensing distance, flush, 600 Hz switching frequency, IP67, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DW-HD-621-M8-100>

Technical Specifications

Brand	Contrinex
Item	Proximity sensor
Sensor Type	Inductive
Application	High temperature
Shape	Tubular
Housing Size	8mm diameter x 60mm body
Housing Material	304 stainless steel
Barrel Type	Threaded
Sensing Method	Extended sensing
Adjustable	No
Number of Wires	3
Switching Output	NPN
Operation Mode	N.O.

Sensing Distance	2mm
Mounting Type	Flush
IO-Link Compatible	No
Switching Frequency	600 Hz
Operating Voltage	10-30 VDC
Operating Temperature	0 to 140C
Weld Field Immune	No
Chip Immune	No
IP Rating	IP67
Connection	Pigtail
Conductor Size	24 AWG
Cable Length	6.5ft/2m
Jacket Material	Silicone

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document