

DGA-15B Cut Sheet



ProSense differential pressure gauge, 4in dial diameter, -15.0 to +15.0in of water column, black die-cast aluminum case, aluminum and silicone rubber wetted parts, (2) high and (2) low 1/8in female NPT process connection, panel or surface mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DGA-15B>

Technical Specifications

| | |
|--------------------|---------------------------------------|
| Brand | ProSense |
| Item | Differential pressure gauge |
| Diameter | 4in dial |
| Scale | -15.0 to +15.0in of water column |
| Case Type | Black die-cast aluminum |
| Wetted Parts | Aluminum and silicone rubber |
| Process Connection | (2) high and (2) low 1/8in female NPT |
| Mounting | Panel or surface |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |