

E2000 Cut Sheet



Marathon XRI premium efficiency AC induction motor, inverter rated, 1hp, 3-phase, 208-230/460 VAC, 3600rpm, TEFC, NEMA 56C frame, rolled steel, C-face/rigid base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/E2000>

Technical Specifications

Brand	Marathon
Item	Motor
Series	XRI
Efficiency Group	Premium efficiency
Efficiency	80
Voltage Type	AC
Motor Type	Induction
Motor Application	Inverter rated
Horsepower Rating	1hp
Number of Phases	3
Voltage Rating	208-230/460 VAC
Synchronous Speed	3600rpm
Nameplate RPM	3490rpm
Overload Type	None
Enclosure Type	TEFC
Shaft Type	Round with square key

Shaft Diameter	5/8in
Shaft Material	1144 Stressproof (C-223) steel
Motor Frame	NEMA 56C
Frame Material	Rolled steel
Electrically Reversible	Yes
Insulation Class	Class F
IP Rating	IP43
Constant Torque Rating	10:1
Variable Torque Rating	10:1
Service Factor	1.15
Integrated Brake	No
NEMA Design	Design B
Junction Box Orientation	F3
Mounting	C-face/rigid base
Mounting Orientation	Horizontal
Manufacturer Part Number	56T34F5940

Agency Approvals

UL Listed File #	None
UL Recognized File #	E49747
UL Hazardous File #	None
CE	View CE declarations
CSA File #	002025
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/E2000.pdf>
See store item page for other formats.