

DMR-0P-1A Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, metal housing, through-beam receiver, 4m sensing distance, 10-30 VDC operating voltage, selectable light-on/dark-on, PNP, 4-wire, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DMR-0P-1A>

Technical Specifications

Brand	AutomationDirect	Number of Wires	4
Item	Photoelectric sensor	Switching Output	PNP
Shape	Tubular	Sensing Distance	4m
Barrel Type	Threaded	Operation Mode	Selectable light-on/dark-on
Housing Size	12mm diameter x 55mm body	Switching Frequency	250 Hz
IP Rating	IP67	Cable Length	6.5ft/2m
Housing Material	Metal	Connection	Pigtail
Sensing Method	Through-beam receiver	Conductor Size	26 AWG
Operating Voltage	10-30 VDC	Includes	Mounting hardware

Agency Approvals

UL Listed File #	E187310
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document