

DN-F10 Cut Sheet



DINnector screw circuit protection terminal block, accepts wire size 24-10 AWG, gray, 6.3A, 35mm DIN rail mount, 10kA SCCR. Package of 50. For use with GMA, GMC, S500 and S506 series fuses.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-F10>

Technical Specifications

Brand	DINnector
Item	Terminal block
Connector Type	Screw
Terminal Block Type	Circuit protection
Accepts Fuse Class	Small dimension (5x20mm and 5x25mm)
Wire Size	24-10 AWG
Color	Gray
Amperage Rating	6.3A
Voltage Rating	250 VAC/VDC
Mounting	35mm DIN rail
SCCR Rating	10kA SCCR
Quantity per Pack	50
For Use With	GMA, GMC, S500 and S506 series fuses

Agency Approvals

UL Listed File #	None
UL Recognized File #	E179129
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/DN-F10.pdf>
See store item page for other formats.