

# DW-AD-612-C12P Cut Sheet



Contrinex inductive proximity sensor, rectangular, 12 x 27 x 6.5mm body, polycarbonate housing, top sensing, NPN, N.C. output, 4mm sensing distance, non-flush, 2000 Hz switching frequency, IP67, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DW-AD-612-C12P>

## Technical Specifications

<b>Brand</b>	Contrinex
<b>Item</b>	Proximity sensor
<b>Sensor Type</b>	Inductive
<b>Application</b>	Standard duty and small space
<b>Shape</b>	Rectangular
<b>Housing Size</b>	12 x 27 x 6.5mm body
<b>Housing Material</b>	Polycarbonate
<b>Sensing Face</b>	Top sensing
<b>Sensing Method</b>	Standard sensing
<b>Adjustable</b>	No
<b>Number of Wires</b>	3
<b>Switching Output</b>	NPN
<b>Operation Mode</b>	N.C. output
<b>Sensing Distance</b>	4mm

<b>Mounting Type</b>	Non-flush
<b>IO-Link Compatible</b>	No
<b>Switching Frequency</b>	2000 Hz
<b>Operating Voltage</b>	10-30 VDC
<b>Operating Temperature</b>	-25 to 70 deg C
<b>Weld Field Immune</b>	No
<b>Chip Immune</b>	No
<b>IP Rating</b>	IP67
<b>Connection</b>	Pigtail
<b>Conductor Size</b>	26 AWG
<b>Cable Length</b>	6.5ft/2m
<b>Jacket Material</b>	PVC
<b>Includes</b>	Mounting hardware

## Agency Approvals

<b>UL Listed File #</b>	NRKH.E239373
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>