

FCAL75 Cut Sheet

Laumas bending beam load cell, 165 lb/75 kg, +/- 0.017% of full scale accuracy, voltage signal range(s) of 2 mV/V, 3-15 VDC, stainless steel, IP68, 9.8ft/3m integral 4-wire shielded cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FCAL75>



Technical Specifications

Brand	Laumas
Item	Load cell
Sensor Type	Bending beam
Application	Platforms, scales, hoppers, filling, batching, tanks and vessels
Load Rating	165 lb/75 kg
Accuracy	+/- 0.017% of full scale
Output Voltage Signal Range	2 mV/V

Operating Voltage	3-15 VDC
Operating Temperature	-20 to 50 deg C
Material	Stainless steel
IP Rating	IP68
Mounting Hole Size	(3) 13mm
Electrical Connection	9.8ft/3m integral 4-wire shielded cable

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/FCAL75.pdf>
See store item page for other formats.