

DW-AD-712-M18 Cut Sheet



Contrinex inductive proximity sensor, tubular, 18mm diameter x 50mm body, stainless steel housing, NPN, N.C. output, 20mm sensing distance, non-flush, 200 Hz switching frequency, IP68 IP69K, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DW-AD-712-M18>

Technical Specifications

Brand	Contrinex
Item	Proximity sensor
Sensor Type	Inductive
Application	Harsh duty and full metal
Shape	Tubular
Housing Size	18mm diameter x 50mm body
Housing Material	Stainless steel
Barrel Type	Threaded
Sensing Method	Triple sensing
Adjustable	No
Number of Wires	3
Switching Output	NPN
Operation Mode	N.C. output

Sensing Distance	20mm
Mounting Type	Non-flush
IO-Link Compatible	No
Switching Frequency	200 Hz
Operating Voltage	10-30 VDC
Operating Temperature	-25 to 85 deg C
Weld Field Immune	No
Chip Immune	No
IP Rating	IP68 IP69K
Connection	Pigtail
Conductor Size	22 AWG
Cable Length	6.5ft/2m
Includes	Mounting hardware

Agency Approvals

UL Listed File #	E239373
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DW-AD-712-M18.pdf>
See store item page for other formats.