

# FF12D24NN53 Cut Sheet



Fandis Virdis series intake fan, side mount, 21 CFM, 24 VDC operating voltage, G4 (coarse) filter mat, NEMA 3R, safe for outdoor use, 4.92 x 4.92in enclosure cutout, RAL 9005 black.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FF12D24NN53>

## Technical Specifications

<b>Brand</b>	Fandis
<b>Series</b>	Virdis series
<b>Airflow Direction</b>	Intake
<b>Item</b>	Fan
<b>Mounting</b>	Side
<b>With Air Flaps</b>	No
<b>Filter Media</b>	G4 (coarse) filter mat
<b>Free Airflow</b>	21 CFM
<b>Airflow with Grill and Filter(s)</b>	14 CFM
<b>Operating Voltage</b>	24 VDC
<b>Power Consumption</b>	7W
<b>Current Draw</b>	310 mA
<b>Electrical Connection</b>	Screwless terminal block
<b>Maximum Static Pressure</b>	51Pa
<b>Operating Temperature</b>	14 to 131 deg F
<b>Average Noise Level</b>	43 dBA
<b>NEMA Rating</b>	3R
<b>Application</b>	Safe for outdoor use
<b>IP Rating</b>	IP55
<b>Enclosure Cutout</b>	4.92 x 4.92in
<b>Color</b>	RAL 9005 black
<b>Additional Information</b>	Purchase exhaust grille separately

## Agency Approvals

<b>UL Listed File #</b>	E500932
<b>UL Recognized File #</b>	E237844
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	260922
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>