

FG1W-50BP-16 Cut Sheet



ProSense water mechanical flow meter, variable area, 1/2in female NPT process connection, 1 to 16 GPM, 5 to 60 LPM.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FG1W-50BP-16>

Technical Specifications

Brand	ProSense
Item	Mechanical flow meter
Media Type	Water
Sensing Type	Variable area
Process Connection	1/2in female NPT
Measuring Range	1 to 16 GPM
Measuring Range 2	5 to 60 LPM

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document