

# FLHTF1300A115 Cut Sheet



Hammond enclosure heater, axial fan, 1300W heating capacity, incoloy tubular heating element, 120 VAC operating voltage, 60 Hz, adjustable thermostat, N.C. (open on rise) 0 to 100 deg F, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLHTF1300A115>

## Technical Specifications

Brand	Hammond
Item	Enclosure heater
Fan Type	Axial
Heating Capacity	1300W
Heating Element	Incoloy tubular
Operating Voltage	120 VAC
Hertz	60 Hz

Connection	3-pole terminal block for 12 AWG max solid or stranded wire
Heater Control	Adjustable thermostat
Contact 1	N.C. (open on rise) 0 to 100 deg F
Switching Differential	13 deg F
Switching Tolerance	+/-5 deg F
Mounting	Panel

## Agency Approvals

UL Listed File #	E331157
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	LR43697
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/FLHTF1300A115.pdf>  
See store item page for other formats.