

# FLHTF800A115 Cut Sheet



Hammond enclosure heater, axial fan, 800W heating capacity, incoloy tubular heating element, 120 VAC operating voltage, 60 Hz, adjustable thermostat, N.C. (open on rise) 0 to 100 deg F, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLHTF800A115>

## Technical Specifications

<b>Brand</b>	Hammond
<b>Item</b>	Enclosure heater
<b>Fan Type</b>	Axial
<b>Heating Capacity</b>	800W
<b>Heating Element</b>	Incoloy tubular
<b>Operating Voltage</b>	120 VAC
<b>Hertz</b>	60 Hz
<b>Connection</b>	3-pole terminal block for 12 AWG max solid or stranded wire
<b>Heater Control</b>	Adjustable thermostat
<b>Contact 1</b>	N.C. (open on rise) 0 to 100 deg F
<b>Switching Differential</b>	13 deg F
<b>Switching Tolerance</b>	+/-5 deg F
<b>Mounting</b>	Panel

## Agency Approvals

<b>UL Listed File #</b>	E331157
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	LR43697
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>