

FLS-HT-100 Cut Sheet



ProSense float liquid level tilt switch, suspendible/submersible mount, EPDM rubber rectangular float, EPDM rubber rectangular, polypropylene, PVC wetted parts, 32 to 158 deg F, mercury-free SPDT switch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLS-HT-100>

Technical Specifications

Brand	ProSense
Item	Level tilt switch
Sensor Type	Float
Media Type	Liquid
Mounting	Suspendible/submersible
Float	EPDM rubber rectangular
Wetted Parts	EPDM rubber rectangular, polypropylene, PVC
Process Temperature	32 to 158 deg F
Output	Mercury-free SPDT switch
Electrical Connection	22.9ft (7m) cable
Jacket Material	PVC
Includes	Optional polypropylene stabilizing weight

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document