

# FLS-VL-200 Cut Sheet



ProSense float liquid level switch, vertical top mount, 2.63in insertion length, 1.25in diameter float, Buna-N, polybutylene wetted parts, -40 to 221 deg F, 1/4in male NPT process connection, SPST reed switch, N.O./N.C. selectable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLS-VL-200>

## Technical Specifications

|                                      |   |
|--------------------------------------|---|
| <b>Brand</b>                         | ProSense  |
| <b>Item</b>                          | Level switch  |
| <b>Sensor Type</b>                   | Float   |
| <b>Media Type</b>                    | Liquid  |
| <b>Mounting</b>                      | Vertical top  |
| <b>Insertion Length</b>              | 2.63in  |
| <b>Float</b>                         | 1.25in diameter   |
| <b>Process Connection</b>            | 1/4in male NPT  |
| <b>Wetted Parts</b>                  | Buna-N, polybutylene  |
| <b>Process Temperature</b>           | -40 to 221 deg F  |
| <b>Output</b>                        | SPST reed switch, N.O./N.C. selectable                              |
| <b>Electrical Connection</b>         | 24in 22AWG lead wires with stripped ends                            |
| <b>Conductor Insulation Material</b> | Teflon  |
| <b>Additional Information</b>        | Not for use in hot water at temperatures above 149 deg F (65 deg C) |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | E320431                                |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | 259726                                 |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |