

# FSA75-42-6H Cut Sheet



ProSense liquid flow transmitter, spring-supported piston, 3/4in female NPT process connection, 0 to 6 GPM, Output: analog, 4-20 mA, 18-32 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FSA75-42-6H>

## Technical Specifications

Brand	ProSense
Item	Flow transmitter
Media Type	Liquid
Sensing Type	Spring-supported piston
Process Connection	3/4in female NPT
Measuring Range	0 to 6 GPM
Output	Analog, 4-20 mA
Operating Voltage	18-32 VDC
Electrical Connection	4-pin M12 quick-disconnect
Additional Information	Purchase cable separately

## Agency Approvals

UL Listed File #	E320431
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/FSA75-42-6H.pdf>  
See store item page for other formats.