

FSC15-00-42-50H Cut Sheet



ProSense liquid digital flow sensor, spring-supported piston, 1-1/2in female NPT process connection, 0 to 50 GPM, 14 to 212 deg F, Output: switch or frequency, Output 2: switch or current, 18-30 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FSC15-00-42-50H>

Technical Specifications

Brand	ProSense
Item	Digital flow sensor
Media Type	Liquid
Sensing Type	Spring-supported piston
Process Connection	1-1/2in female NPT
Measuring Range	0 to 50 GPM
Measuring Range 2	14 to 212 deg F
Output	Switch (N.O./N.C.) or frequency, PNP/NPN selectable
Output 2	Switch (N.O./N.C.), PNP/NPN selectable or 4-20 mA
Operating Voltage	18-30 VDC
Electrical Connection	4-pin M12 quick-disconnect
Display Type	4-digit, two-color LED display
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E320431
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/FSC15-00-42-50H.pdf>
See store item page for other formats.