

FSD75-AP-6H Cut Sheet



ProSense liquid flow switch, spring-supported piston, 3/4in female NPT process connection, 0.26 to 6.6 GPM, Output: switch PNP, N.O., 20.4 to 26.4 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FSD75-AP-6H>

Technical Specifications

Brand	ProSense
Item	Flow switch
Media Type	Liquid
Sensing Type	Spring-supported piston
Process Connection	3/4in female NPT
Measuring Range	0.26 to 6.6 GPM
Output	Switch PNP, N.O.
Operating Voltage	20.4 to 26.4 VDC
Electrical Connection	4-pin M12 quick-disconnect
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E320431
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document