

FTI26-CO7NWDJ Cut Sheet



Endress+Hauser Nivector capacitance bulk solids level switch, 316L stainless steel, ECTFE wetted parts, G1 male thread process connection, switch PNP, N.O. or N.C., 4-pin M12 quick-disconnect, IP66, IP68 and IP69, NEMA 4X/6P.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FTI26-CO7NWDJ>

Technical Specifications

Brand	Endress+Hauser
Item	Level switch
Series	Nivector
Sensor Type	Capacitance
Media Type	Bulk solids
Mounting	Any orientation
Insertion Length	2.84in/72mm
Process Connection	G1 male thread
Process Temperature	-4 to 167 deg F
Output	Switch PNP, N.O. or N.C.
Operating Voltage	18-30 VDC
Wetted Parts	316L stainless steel, ECTFE

Electrical Connection	4-pin M12 quick-disconnect
IP Rating	IP66, IP68 and IP69
NEMA Rating	4X/6P
Application	Hazardous location rated
IO-Link Compatible	Yes
Communication Port and Connection Type(s)	(1) 4-pin M12 A-coded (IO-Link) port(s)
Port Protocol(s)	IO-Link Class A Device
Port Speed(s)	IO-Link COM2
IO-Link Version	IO-Link v1.1
Standard I/O Mode Supported	Yes

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	053988_C_000
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	3-A Certification/CSA Control Drawing

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/FTI26-CO7NWDJ.pdf>
See store item page for other formats.