

DW-AS-711-M30-002 Cut Sheet



Contrinex inductive proximity sensor, tubular, 30mm diameter x 63.5mm body, stainless steel housing, NPN, N.O. output, 40mm sensing distance, non-flush, 90 Hz switching frequency, IP68 IP69K, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DW-AS-711-M30-002>

Technical Specifications

| | |
|-------------------------|---------------------------------------|
| Brand | Contrinex |
| Item | Proximity sensor |
| Sensor Type | Inductive |
| Application | Harsh duty, full metal and long range |
| Shape | Tubular |
| Housing Size | 30mm diameter x 63.5mm body |
| Housing Material | Stainless steel |
| Barrel Type | Threaded |
| Sensing Method | Triple sensing |
| Adjustable | No |
| Number of Wires | 3 |
| Switching Output | NPN |
| Operation Mode | N.O. output |

| | |
|-------------------------------|----------------------------|
| Sensing Distance | 40mm |
| Mounting Type | Non-flush |
| IO-Link Compatible | No |
| Switching Frequency | 90 Hz |
| Operating Voltage | 10-30 VDC |
| Operating Temperature | -25 to 85c |
| Weld Field Immune | No |
| Chip Immune | No |
| IP Rating | IP68 IP69K |
| Connection | 4-pin M12 quick-disconnect |
| Includes | Mounting hardware |
| Additional Information | Purchase cable separately |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E239373 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |