

# DW-AS-713-M30-967 Cut Sheet



Contrinex inductive proximity sensor, tubular, 30mm diameter x 63.5mm body, 304 stainless steel housing, PNP, N.O., 12mm sensing distance, non-flush, 90 Hz switching frequency, IP68 IP69K, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DW-AS-713-M30-967>

## Technical Specifications

<b>Brand</b>	Contrinex
<b>Item</b>	Proximity sensor
<b>Sensor Type</b>	Inductive
<b>Application</b>	Machining
<b>Shape</b>	Tubular
<b>Housing Size</b>	30mm diameter x 63.5mm body
<b>Housing Material</b>	304 stainless steel
<b>Barrel Type</b>	Threaded
<b>Sensing Method</b>	Standard sensing
<b>Adjustable</b>	No
<b>Number of Wires</b>	3
<b>Switching Output</b>	PNP
<b>Operation Mode</b>	N.O.
<b>Sensing Distance</b>	12mm
<b>Mounting Type</b>	Non-flush
<b>IO-Link Compatible</b>	Yes

<b>Switching Frequency</b>	90 Hz
<b>Operating Voltage</b>	10-30 VDC
<b>Operating Temperature</b>	-25 to 85 deg C
<b>Weld Field Immune</b>	No
<b>Chip Immune</b>	Yes
<b>IP Rating</b>	IP68 IP69K
<b>Connection</b>	4-pin M12 quick-disconnect
<b>Communication Port and Connection Type(s)</b>	(1) 4-pin M12 A-coded (IO-Link) port(s)
<b>Port Protocol(s)</b>	IO-Link Class A Device
<b>Port Speed(s)</b>	IO-Link COM2
<b>IO-Link Version</b>	IO-Link v1.1
<b>Standard I/O Mode Supported</b>	Yes
<b>Includes</b>	Mounting hardware
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	NRKH.E239373
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/DW-AS-713-M30-967.pdf>  
See store item page for other formats.