

DW-HD-611-M30-411 Cut Sheet



Contrinex inductive proximity sensor, tubular, 30mm diameter x 83mm body, 304 stainless steel housing, NPN, N.O., 15mm sensing distance, non-flush, 150 Hz switching frequency, IP67, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DW-HD-611-M30-411>

Technical Specifications

Brand	Contrinex
Item	Proximity sensor
Sensor Type	Inductive
Application	High temperature
Shape	Tubular
Housing Size	30mm diameter x 83mm body
Housing Material	304 stainless steel
Barrel Type	Threaded
Sensing Method	Standard sensing
Adjustable	No
Number of Wires	3
Switching Output	NPN
Operation Mode	N.O.
Sensing Distance	15mm

Mounting Type	Non-flush
IO-Link Compatible	No
Switching Frequency	150 Hz
Operating Voltage	10-30 VDC
Operating Temperature	0 to 230C
Weld Field Immune	No
Chip Immune	No
IP Rating	IP67
Connection	Pigtail
Conductor Size	26 AWG
Cable Length	16.4ft/5m
Jacket Material	PTFE/PUR
Additional Information	Cable consists of 3m PTFE to amplifier and 2m PUR pigtail

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/DW-HD-611-M30-411.pdf>
See store item page for other formats.