

E261A Cut Sheet



Marathon standard efficiency AC induction motor, general purpose, 1/2hp, 1-phase, 100-120/200-240 VAC, 1800rpm, ODP, NEMA 56C frame, rolled steel, C-face/rigid base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/E261A>

Technical Specifications

Brand	Marathon
Item	Motor
Efficiency Group	Standard efficiency
Efficiency	76.2
Voltage Type	AC
Motor Type	Induction
Motor Application	General purpose
Horsepower Rating	1/2hp
Number of Phases	1
Voltage Rating	100-120/200-240 VAC
Synchronous Speed	1800rpm
Nameplate RPM	1725rpm
Overload Type	Automatic
Enclosure Type	ODP

Shaft Type	Round with square key
Shaft Diameter	5/8in
Shaft Material	1144 Stressproof (C-223) steel
Motor Frame	NEMA 56C
Frame Material	Rolled steel
Electrically Reversible	Yes
Insulation Class	Class B
IP Rating	IP22
Service Factor	1.25
Integrated Brake	No
Junction Box Orientation	F1
Mounting	C-face/rigid base
Mounting Orientation	Horizontal
Manufacturer Part Number	056B17D11029

Agency Approvals

UL Listed File #	None
UL Recognized File #	E49747
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR2025
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/E261A.pdf>
See store item page for other formats.