

F18I2-0N-0E Cut Sheet



ProSense photoelectric sensor, tubular, threaded, diffuse, infrared light emission, 100mm sensing distance, selectable light-on/dark-on, NPN, 500 Hz switching frequency, polybutylene terephthalate housing, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F18I2-0N-0E>

Technical Specifications

Brand	ProSense
Item	Photoelectric sensor
Shape	Tubular
Barrel Type	Threaded
Housing Size	18mm diameter x 71.5mm body
IP Rating	IP67
Housing Material	Polybutylene terephthalate
Sensing Method	Diffuse
Operating Voltage	10-30 VDC
Switching Output	NPN
Sensing Distance	100mm
Operation Mode	Selectable light-on/dark-on
Switching Frequency	500 Hz
Light emission	Infrared
IO-Link Compatible	No
Connection	4-pin M12 quick-disconnect
Includes	Mounting hardware
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	NRKH E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	60497-5-2-14
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document