

F18IR-0N-0A Cut Sheet



ProSense photoelectric sensor, tubular, threaded, polybutylene terephthalate housing, through-beam receiver, 25m sensing distance, 10-30 VDC operating voltage, selectable light-on/dark-on, NPN, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F18IR-0N-0A>

Technical Specifications

Brand	ProSense
Item	Photoelectric sensor
Shape	Tubular
Barrel Type	Threaded
Housing Size	18mm diameter x 67mm body
IP Rating	IP67
Housing Material	Polybutylene terephthalate
Sensing Method	Through-beam receiver
Operating Voltage	10-30 VDC
Switching Output	NPN
Sensing Distance	25m
Operation Mode	Selectable light-on/dark-on
Switching Frequency	250 Hz
IO-Link Compatible	No
Cable Length	6.5ft/2m
Jacket Material	PVC
Connection	Pigtail
Conductor Size	26 AWG
Includes	Mounting hardware

Agency Approvals

UL Listed File #	NRKH E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	60497-5-2-14
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document