

# GWR-1600-C Cut Sheet



ProSense coaxial guided wave radar water and oil level sensor, 1570mm maximum sensing range, Output: switch, Output 2: switch or analog, 18 to 30 VDC operating voltage, G3/4 male BSPP process connection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GWR-1600-C>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Level sensor
<b>Sensor Type</b>	Coaxial guided wave radar
<b>Media Type</b>	Water and oil
<b>Sensing Range</b>	1570mm maximum
<b>Output</b>	Switch (N.O./N.C.), PNP/NPN selectable
<b>Output 2</b>	Switch (N.O./N.C.), PNP/NPN selectable or 4-20 mA
<b>Operating Voltage</b>	18 to 30 VDC
<b>Housing Rating</b>	IP68 IP69K
<b>Process Connection</b>	G3/4 male BSPP
<b>Electrical Connection</b>	4-pin M12 quick-disconnect
<b>Requires</b>	GWR-P series level sensing probe and GWR-C series coaxial tube and cable
<b>Additional Information</b>	Level sensing probe and coaxial tube can be cut to adapt to different applications

## Agency Approvals

<b>UL Listed File #</b>	E328811
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>