

H30FUUG0 Cut Sheet



WON H30 series standard bearing block, full ball recirculating bearing, flanged, end seal, carbon steel. For use with H30 series rails.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H30FUUG0>

Technical Specifications

Brand	WON
Item	Standard bearing block
Series	H30
Bearing Type	Full ball recirculating bearing
Block Type	Flanged
Seal Type	End seal
Material	Carbon steel
Precision Class	Moderate precision
Bearing Pre-load	Normal preload
Mass	1100g
Static Load Rating (CO)	57100N
Dynamic Load Rating (C)	38400N
Pitch Moment Load Rating (Mp)	711 N-m
Pitch Moment Load Rating, 2 Bearings (Mp2)	3384 N-m
Yaw Moment Load Rating (My)	711 N-m
Yaw Moment Load Rating, 2 Bearings (My2)	3384 N-m
Roll Moment Load Rating (Mr)	828 N-m
For Use With	H30 series rails

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement