


H805702-1 Cut Sheet



Helukabel HELUKAT flexible Cat5e industrial Ethernet cable, overall shielded, 2 twisted pairs, 26 AWG, 7-stranded, bare copper, foam polyethylene conductor insulation material, PUR jacket, blue, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H805702-1>

Technical Specifications

Brand	Helukabel
Item	Cable
Series	HELUKAT
Protocol	Ethernet
Wire/Cable Type	Cat5e industrial Ethernet
UL Wire/Cable Type	AWM
Applicable Standards	Halogen free and UL 21576
Application	Data
Flexibility	Flexible
Voltage Rating	1000V
Conductors	2 twisted pairs
Conductor Size	26 AWG
Conductor Stranding	7-stranded
Conductor Material	Bare copper

Conductor Insulation Material	Foam polyethylene
Conductor Insulation Color	Pair 1: orange, white/orange and Pair 2: green, white/green
Shielding	Overall aluminum foil and tinned braid
Jacket Material	PUR
Jacket Color	Blue
Nominal Overall Cable Diameter	0.224in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 20 to 99ft = Coil• 100 to 775ft = 14 x 7in Reel• 776 to 1110ft = 14 x 10in Reel• 1111 to 1700ft = 16 x 10in Reel• 1701 to 2380ft = 18 x 10in Reel• 2381 to 2500ft = 18 x 13in Reel

Agency Approvals

UL Listed File #	E170315
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	None