

FF13PA115UF Cut Sheet



Fandis Virdis series intake fan, side mount, 65 CFM, 115 VAC operating voltage, G3 (coarse) filter mat, NEMA 12, indoor use only, 6.97 x 6.97in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FF13PA115UF>

Technical Specifications

Brand	Fandis	Electrical Connection	Screwless terminal block
Series	Virdis series	Maximum Static Pressure	60Pa
Airflow Direction	Intake	Operating Temperature	14 to 131 deg F
Item	Fan	Average Noise Level	49 dBA
Mounting	Side	NEMA Rating	12
With Air Flaps	No	Application	Indoor use only
Filter Media	G3 (coarse) filter mat	IP Rating	IP54
Free Airflow	65 CFM	Enclosure Cutout	6.97 x 6.97in
Airflow with Grill and Filter(s)	44 CFM	Color	RAL 7035 light gray
Operating Voltage	115 VAC	Additional Information	Purchase exhaust grille separately. Fan will also safely operate at 50Hz, but with reduced airflow. Refer to technical specifications for 50Hz performance data
Frequency	50/60 Hz		
Power Consumption	19W		
Current Draw	202 mA		

Agency Approvals

UL Listed File #	E500932
UL Recognized File #	E237844
UL Hazardous File #	None
CE	View CE declarations
CSA File #	260922
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document