

# FFIH-X0-1E Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, 316L stainless steel housing, through-beam emitter, infrared, 20m sensing distance, 10-30 VDC operating voltage, 3-wire, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FFIH-X0-1E>

## Technical Specifications

Brand	AutomationDirect
Item	Photoelectric sensor
Shape	Tubular
Barrel Type	Threaded
Housing Size	18mm diameter x 82.5mm body
IP Rating	IP69K
Application	For harsh duty / food and beverage applications
Housing Material	316L stainless steel

Sensing Method	Through-beam emitter
Operating Voltage	10-30 VDC
Number of Wires	3
Sensing Distance	20m
Light Emission (NP)	Infrared
Connection	4-pin M12 quick-disconnect
Includes	Mounting hardware
Additional Information	Purchase cable separately

## Agency Approvals

UL Listed File #	E187310
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/FFIH-X0-1E.pdf>  
See store item page for other formats.