

FKLD-BN-3E Cut Sheet



AchieVe photoelectric sensor, tubular, threaded, nickel-plated brass housing, through-beam receiver, 90-degree, 0.05-50m sensing distance, 10-30 VDC operating voltage, complementary light-on/dark-on, NPN, 4-wire, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FKLD-BN-3E>

Technical Specifications

Brand	AchieVe
Item	Photoelectric sensor
Shape	Tubular
Barrel Type	Threaded
Housing Size	18mm diameter x 60mm body
IP Rating	IP67
Application	Laser and standard duty
Housing Material	Nickel-plated brass
Sensing Method	Through-beam receiver
Head Angle	90-degree
Operating Voltage	10-30 VDC

Number of Wires	4
Switching Output	NPN
Sensing Distance	0.05-50m
Sensitivity	Potentiometer
Operation Mode	Complementary light-on/dark-on
Switching Frequency	1 kHz
IO-Link Compatible	No
User Interface	Potentiometer adjustment
Connection	4-pin M12 quick-disconnect
Includes	Mounting hardware
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/FKLD-BN-3E.pdf>
See store item page for other formats.