


# HPX1-BB3P-2SP Cut Sheet



IronHorse busbar, 64A, 600 VAC, cut to length not permitted, connects up to 2 HMMP-32H Manual motor protectors without accessories. Use HPX1-PTB-MP power terminal to connect feeder.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HPX1-BB3P-2SP>

## Technical Specifications

Brand	IronHorse
Item	Busbar
Amperage Rating	64A
Voltage Rating	600 VAC
Cut to Length	Not permitted
Application	Connects up to 2 HMMP-32H Manual motor protectors without accessories. Use HPX1-PTB-MP power terminal to connect feeder

## Agency Approvals

UL Listed File #	E195426
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/HPX1-BB3P-2SP.pdf>  
See store item page for other formats.