

FLHTF800A230 Cut Sheet



Hammond enclosure heater, axial fan, 670/800W heating capacity, incoloy tubular heating element, 220-240 VAC operating voltage, 50/60 Hz, adjustable thermostat, N.C. (open on rise) 0 to 100 deg F, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLHTF800A230>

Technical Specifications

Brand	Hammond
Item	Enclosure heater
Fan Type	Axial
Heating Capacity	670/800W
Heating Element	Incoloy tubular
Operating Voltage	220-240 VAC
Hertz	50/60 Hz
Connection	3-pole terminal block for 12 AWG max solid or stranded wire
Heater Control	Adjustable thermostat
Contact 1	N.C. (open on rise) 0 to 100 deg F
Switching Differential	13 deg F
Switching Tolerance	+/-5 deg F
Mounting	Panel

Agency Approvals

UL Listed File #	E331157
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	LR43697
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	RoHS Statement