

# FSA1-42-27H Cut Sheet



ProSense liquid flow transmitter, spring-supported piston, 1in female NPT process connection, 0 to 27 GPM, Output: analog, 4-20 mA, 18 to 32 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FSA1-42-27H>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Flow transmitter
<b>Media Type</b>	Liquid
<b>Sensing Type</b>	Spring-supported piston
<b>Process Connection</b>	1in female NPT
<b>Measuring Range</b>	0 to 27 GPM
<b>Output</b>	Analog, 4-20 mA
<b>Operating Voltage</b>	18 to 32 VDC
<b>Electrical Connection</b>	4-pin M12 quick-disconnect
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	E320431
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>