

FSD1-AP-26H Cut Sheet



ProSense liquid flow switch, spring-supported piston, 1in female NPT process connection, 1.32 to 26.4 GPM, Output: switch PNP, N.O., 20.4 to 26.4 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FSD1-AP-26H>

Technical Specifications

| | |
|------------------------|----------------------------|
| Brand | ProSense |
| Item | Flow switch |
| Media Type | Liquid |
| Sensing Type | Spring-supported piston |
| Process Connection | 1in female NPT |
| Measuring Range | 1.32 to 26.4 GPM |
| Output | Switch PNP, N.O. |
| Operating Voltage | 20.4 to 26.4 VDC |
| Electrical Connection | 4-pin M12 quick-disconnect |
| Additional Information | Purchase cable separately |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E320431 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |