

IHCC512 Cut Sheet



International Power regulated linear power supply, 5 VDC @ 6A/30W and 12–15 VDC @ 2.5A/30W, 120 VAC and 240 VAC nominal input, 1-phase, open frame, aluminum housing, chassis mount, turret terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/IHCC512>

Technical Specifications

Brand	International Power
Item	Power supply
Power Supply Type	Regulated linear
Efficiency	45% @ 120 VAC
Output Configuration	Dual output
Output	5 VDC @ 6A/30W
Output 2	12–15 VDC @ 2.5A/30W
Input voltage range	120/240 VAC
Input Voltage Selection Type	Jumper
Number of Input Phases	1
Protection Type(s)	<ul style="list-style-type: none">• short circuit• overload• overvoltage

Remote On/Off	No
Voltage Monitoring	No
Enclosure Type	Open frame
Housing Material	Aluminum
Mounting	Chassis
Connector Type	Turret terminals
NEC Class 2	No
Integrated UPS Battery Control	No
Operating Temperature	0–50 °C

Agency Approvals

UL Listed File #	None
UL Recognized File #	E133338
UL Hazardous File #	None
CE	View CE declarations
CSA File #	C22.2 No. 1950
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/IHCC512.pdf>
See store item page for other formats.