

# FTI26-CA7MWDJ Cut Sheet



Endress+Hauser Nivector capacitance bulk solids level switch, 316L stainless steel, ECTFE wetted parts, G1 male thread process connection, switch PNP, N.O. or N.C., 4-pin M12 quick-disconnect, IP65 and IP67, NEMA 4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FTI26-CA7MWDJ>

## Technical Specifications

<b>Brand</b>	Endress+Hauser
<b>Item</b>	Level switch
<b>Series</b>	Nivector
<b>Sensor Type</b>	Capacitance
<b>Media Type</b>	Bulk solids
<b>Mounting</b>	Any orientation
<b>Insertion Length</b>	2.84in/72mm
<b>Process Connection</b>	G1 male thread
<b>Process Temperature</b>	-4 to 176 deg F
<b>Output</b>	Switch PNP, N.O. or N.C.
<b>Operating Voltage</b>	18-30 VDC
<b>Wetted Parts</b>	316L stainless steel, ECTFE

<b>Electrical Connection</b>	4-pin M12 quick-disconnect
<b>IP Rating</b>	IP65 and IP67
<b>NEMA Rating</b>	4X
<b>IO-Link Compatible</b>	Yes
<b>Communication Port and Connection Type(s)</b>	(1) 4-pin M12 A-coded (IO-Link) port(s)
<b>Port Protocol(s)</b>	IO-Link Class A Device
<b>Port Speed(s)</b>	IO-Link COM2
<b>IO-Link Version</b>	IO-Link v1.1
<b>Standard I/O Mode Supported</b>	Yes

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	053988_C_000
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">3-A Certification</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/FTI26-CA7MWDJ.pdf>  
See store item page for other formats.