

# KMF310V Cut Sheet



Roxburgh EMI input filter, 575 VAC, 3-phase, 10A, panel mount, EMI/RFI filtering, 2-stage, drive rated, high performance, screw terminals. For use with 3-phase AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KMF310V>

## Technical Specifications

Brand	Roxburgh
Item	Input filter
Filter Type	EMI
Filter Voltage Rating	575 VAC
Number of Input Phases	3
Amperage Rating	10A
On/Off Switch	No
Fused	No

Mounting	Panel
Filtering	EMI/RFI
Number of Filter Stages	2
SCCR Rating	5kA SCCR
Filter Application	Drive rated
Filter Performance Level	High performance
Connector Type	Screw terminals
For Use With	3-phase AC drives

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E191581
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/KMF310V.pdf>  
See store item page for other formats.