

# LH5946-PC-24-04 Cut Sheet



Dold safety relay, motor standstill monitoring, 20-400 mV, 2-channel, 24 VDC, (3) N.O. and (1) N.C. safety output(s), push-in cage clamp.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LH5946-PC-24-04>

## Technical Specifications

<b>Brand</b>	Dold
<b>Item</b>	Safety relay
<b>Relay Type</b>	Motor standstill monitoring
<b>Monitoring Circuit</b>	20-400 mV
<b>Number Of Channels</b>	2
<b>Control Voltage</b>	24 VDC
<b>Restart Type</b>	Manual or automatic restart
<b>Safety Output Type</b>	(3) N.O. and (1) N.C.
<b>Connection</b>	Push-in cage clamp
<b>Additional Information</b>	(2) redundant measuring channels used for L2-L1 and L3-L1

## Agency Approvals

<b>UL Listed File #</b>	E107778
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/LH5946-PC-24-04.pdf>  
See store item page for other formats.