

# G32M200MD-MC Cut Sheet



NITRA pneumatic cylinder, ISO 15552, 32mm bore, 12mm rod diameter, 200mm stroke, double acting, magnetic piston, adjustable cushions.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/G32M200MD-MC>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Cylinder
<b>Working Fluid</b>	Air or inert gas
<b>Cylinder Type</b>	ISO 15552
<b>Bore Diameter</b>	32mm
<b>Stroke</b>	200mm
<b>Port Size</b>	G1/8 female BSPP
<b>Action Type</b>	Double acting

<b>Magnetic Piston</b>	Yes
<b>Adjustable Cushions</b>	Yes
<b>Body Material</b>	Aluminum
<b>End Cap Material</b>	Aluminum
<b>Rod Material</b>	Chrome-plated steel
<b>Rod Diameter</b>	12mm
<b>Rod Thread Size</b>	M10 x 1.25 male ISO
<b>Maximum Operating Pressure</b>	145 psi

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/G32M200MD-MC.pdf>  
See store item page for other formats.