

# LS7-502WC9-RYGBC Cut Sheet



Patlite LED signal tower, (5) tiers, 70mm diameter, red/amber/green/blue/clear, permanent light function, 24 VDC, NPN/PNP polarity, clear lens, 230mm body length, off-white, 360 degree viewing angle, direct mount, IP69K.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LS7-502WC9-RYGBC>

## Technical Specifications

|                            |   |
|----------------------------|---|
| <b>Brand</b>               | Patlite   |
| <b>Item</b>                | Signal tower                                      |
| <b>Bulb Type</b>           | LED   |
| <b>Number Of Tiers</b>     | 5   |
| <b>Diameter</b>            | 70mm  |
| <b>Light Color(s)</b>      | Red/amber/green/blue/clear                        |
| <b>Light Function</b>      | Permanent   |
| <b>Voltage Rating</b>      | 24 VDC  |
| <b>Polarity</b>            | NPN/PNP   |
| <b>Lens Type</b>           | Clear   |
| <b>Body Length</b>         | 230mm   |
| <b>Body Color</b>          | Off-white   |
| <b>Body Material</b>       | ABS plastic                                       |
| <b>Tower Viewing Angle</b> | 360 degree  |
| <b>Connector Type</b>      | 8-pin M12 quick-disconnect                        |
| <b>Mounting</b>            | Direct  |
| <b>IP Rating</b>           | IP69K   |
| <b>Application</b>         | High-temperature, high-pressure and washdown safe |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | E215660                                |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |