

# GS2-10P2 Cut Sheet



GS2 series AC micro drive, enclosed, 1/4hp with 1-phase input, V/Hz mode, A frame, RS-232/RS-485.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GS2-10P2>

## Technical Specifications

Item	Drive
Controller Type	Micro
Series	GS2
Voltage Type	AC
Number of Input Phases	1
Number of Output Phases	3
Horsepower By Input Phase	1/4hp with 1-phase input
Amperage Rating	1.6A
Variable Torque Amperage Rating	1.6A
Control Mode	V/Hz
Safe Torque Off (STO)	No
Temperature Rating	-10 to 50 deg C
Enclosure Type	Enclosed
IP Rating	IP20

Mounting	35mm DIN rail, panel or wall
Frame Size	A
Communication Port and Connection Type(s)	(1) RS-232/RS-485 (RJ12)
Port Protocol(s)	<ul style="list-style-type: none"><li>• Modbus RTU</li><li>• Modbus ASCII</li></ul>
Port Speed(s)	up to 38.4k baud
Input Signal	4-20 mA, voltage or potentiometer input
Output Type	PWM output
Reverse Capability	Built-in
Internally Bypassed	No
Carrier Frequency Range	1-12 kHz
Output Frequency Range	0.1-400 Hz
Connector Type	Screw terminals
For Use With	3-phase induction motors

## Agency Approvals

UL Listed File #	E198015
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/GS2-10P2.pdf>  
See store item page for other formats.