

MHSELE01 Cut Sheet



MK Morse hole saw set, 29 pieces, carbide tipped steel and bi-metal cobalt, hardened steel backer, varied tooth.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MHSELE01>

Technical Specifications

Brand	MK Morse
Item	Hole saw set
Number of Pieces	29
Material	Carbide tipped steel and bi-metal cobalt
Hole Saw Size	3/4in (19mm), 7/8in (22mm), 1in (25mm), 1-1/8in (29mm), 1-1/4in (32mm), 1-3/8in (35mm), 1-1/2in (38mm), 1-3/4in (44mm), 2in (51mm), 2-1/4in (57mm), 2-1/2in (64mm), 3in (76mm), 3-5/8in (92mm), 4-1/8in (105mm), 4-1/2in (114mm) and 4-3/4in (121mm)
Cutting Direction	Right hand
Hardened Steel Backer	Yes
Tooth Density	4/6 teeth/in
Toothing	Varied tooth

Set Includes	Includes (15) bi-metal hole saws (3/4in, 7/8in, 1in, 1-1/8in, 1-1/4in, 1-3/8in, 1-1/2in, 1-3/4in, 2in, 2-1/2in, 3in, 3-5/8in, 4-1/8in, 4-1/2in and 4-3/4in), (9) carbide tipped hole saws (3/4in, 7/8in, 1-1/8in, 1-3/8in, 1-1/2in, 1-3/4in, 2in, 2-1/4in and 2-1/2in), (1) 3/8in hex standard arbor assembly, (1) 3/8in hex pinned arbor assembly, (2) replacement 1/4in pilot drills, (1) tool storage case
Application	Hole cutting
For Use On	Steel, stainless steel, aluminum, wood, plastic and composite
Additional Information	Includes storage case

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement