

# MS10M-12G-B Cut Sheet



NITRA pneumatic push-to-connect fitting, straight, nickel-plated brass body, nickel-plated brass threads, thread sealant, (1) G1/2 male BSPP to (1) 10mm push-to-connect. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MS10M-12G-B>

## Technical Specifications

|                          |   |
|--------------------------|---|
| Brand                    | NITRA   |
| Item                     | Fitting   |
| Working Fluid            | Air or inert gas                                |
| Fitting Connection Type  | Push-to-connect                                 |
| Fitting Type             | Straight  |
| Body Material            | Nickel-plated brass                             |
| Thread Material          | Nickel-plated brass                             |
| Thread Sealant           | Yes   |
| Fitting Measurement Type | Metric and SAE                                  |
| Connection               | (1) G1/2 male BSPP and (1) 10mm push-to-connect |
| Operating Pressure       | 0 to 300 psi                                    |
| Operating Temperature    | 0 to 175 deg F                                  |
| Quantity per Pack        | 5   |
| For Use With             | Flexible pneumatic tubing                       |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/MS10M-12G-B.pdf>  
See store item page for other formats.