

GS4-2060 Cut Sheet



DURApulse GS4 series AC high-performance drive, open frame, 230 VAC, 60hp with 3-phase input, 15hp with 1-phase input, SVC or V/Hz mode, E frame, RS-485, Modbus and BACnet, 100kA SCCR. Optional EtherNet/IP and Modbus TCP cards available.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GS4-2060>

Technical Specifications

Brand	DURApulse
Item	Drive
Controller Type	High-performance
Series	GS4
Voltage Type	AC
Nominal Drive Input Voltage	230 VAC
Nominal Drive Output Voltage	230 VAC
Number of Input Phases	3 and 1
Number of Output Phases	3
Horsepower By Input Phase	60hp with 3-phase input, 15hp with 1-phase input
Amperage Rating	161A with 3-phase input and 49A with 1-phase input
Variable Torque Amperage Rating	180A
Control Mode	SVC or V/Hz
Safe Torque Off (STO)	Yes
Temperature Rating	-10 to 50 deg C
Enclosure Type	Open frame
IP Rating	IP00 and IP20
Mounting	Wall
Frame Size	E
Dynamic Braking	External dynamic braking unit required
Communication Port and Connection Type(s)	(1) RS-485 (RJ12)
Port Protocol(s)	<ul style="list-style-type: none"> • Modbus RTU • Modbus ASCII • BACnet
Port Speed(s)	up to 115.2k baud
Input Signal	4-20 mA, voltage or potentiometer input
Output Type	PWM output
Reverse Capability	Built-in
Internally Bypassed	No

Carrier Frequency Range	2-15 kHz
Output Frequency Range	0.1-599 Hz
Number of Analog Input Channels	3
Number Of Input Channels	3
Analog Input Signal Type	Current/voltage
Number of Non-Isolated Analog Input Commons	1
Number of Points per Analog Input Common	3
Input Resolution	11-bit
Input Current Signal Range	0-20 mA, 4-20 mA
Input Voltage Signal Range	+/- 10 VDC
Number of Analog Output Channels	2
Number Of Output Channels	2
Analog Output Signal Type	Current/voltage
Number of Non-Isolated Analog Output Commons	1
Number of Points per Analog Output Common	2
Output Resolution	10-bit
Output Current Signal Range	0-20 mA and 4-20 mA
Output Voltage Signal Range	0-10 VDC
Number of Discrete Input Points	8
Nominal Discrete Input Voltage	24 VDC
Discrete Input Type	Sinking/sourcing
Number of Non-Isolated Discrete Input Commons	1
Number of Points per Discrete Input Common	8

GS4-2060 Cut Sheet

Number of Discrete Output Points	4
Nominal Discrete Output Voltage	240 VAC and 48 VDC
Discrete Output Type	Relay/sinking/sourcing
Relay Configuration	(2) Form C (SPDT) relays
Number of Non-Isolated Discrete Output Commons	1
Number of Isolated Discrete Output Commons	2
Number of Points per Discrete Output Common	2
Load Current	3A/point relay, 50 mA/point discrete
Fuse Type	User-supplied external fuse
Programming Language	Ladder
SCCR Rating	100kA SCCR
Connector Type	Screw terminals
For Use With	3-phase induction motors
Additional Information	Optional EtherNet/IP and Modbus TCP cards available

Agency Approvals

UL Listed File #	E198015
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document