


# H15FUUG0 Cut Sheet



WON H15 series standard bearing block, full ball recirculating bearing, flanged, end seal, carbon steel. For use with H15 series rails.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H15FUUG0>

## Technical Specifications

<b>Brand</b>	WON
<b>Item</b>	Standard bearing block
<b>Series</b>	H15
<b>Bearing Type</b>	Full ball recirculating bearing
<b>Block Type</b>	Flanged
<b>Seal Type</b>	End seal
<b>Material</b>	Carbon steel
<b>Precision Class</b>	Moderate precision
<b>Bearing Pre-load</b>	Normal preload
<b>Mass</b>	190g
<b>Static Load Rating (CO)</b>	16200N
<b>Dynamic Load Rating (C)</b>	9900N
<b>Pitch Moment Load Rating (Mp)</b>	115 N-m
<b>Pitch Moment Load Rating, 2 Bearings (Mp2)</b>	552 N-m
<b>Yaw Moment Load Rating (My)</b>	115 N-m
<b>Yaw Moment Load Rating, 2 Bearings (My2)</b>	552 N-m
<b>Roll Moment Load Rating (Mr)</b>	129 N-m
<b>For Use With</b>	H15 series rails

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>