


HBR-67-120-A Cut Sheet



IronHorse heavy-duty helical bevel gearbox, 120:1 ratio, 56C-Face input, hollow, 1.5in diameter output shaft, nominal 1hp at 1.88 SF, 7260 lb-in mechanical output torque, Type-67 frame, cast iron housing, vertical or horizontal mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HBR-67-120-A>

Technical Specifications

| | |
|--------------------------------------|-----------------------------------|
| Brand | IronHorse |
| Item | Gearbox |
| Application | General purpose |
| Duty Rating | Heavy-duty |
| Gearbox Type | Helical bevel |
| Gear Ratio | 120:1 |
| Speed Rating | 1750rpm input / 15rpm output |
| Input Configuration | 56C-Face |
| Input Power Rating | Nominal 1hp at 1.88 SF |
| Output Configuration | Hollow |
| Gearbox Output Shaft Diameter | 1.5in |
| Mechanical Output Torque | 7260 lb-in |
| Frame | Type-67 |
| Housing Material | Cast iron |
| Mounting | Vertical or horizontal |
| Finish | Anti-corrosion primer and paint |
| Lubrication Type | Pre-filled with HD320 mineral oil |
| Oil Seal Type | Double-lip |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | none |
| UL Recognized File # | none |
| UL Hazardous File # | none |
| CE | None |
| CSA File # | none |
| RoHS Status | No |
| EU REACH | View EU REACH document |