

# NA-403-1 Cut Sheet



Penn-Union neutral bar, tin-plated aluminum, 6 openings, 5 circuits, mounting hole position 3, copper or aluminum, AL9CU.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NA-403-1>

## Technical Specifications

<b>Brand</b>	Penn-Union
<b>Item</b>	Neutral bar
<b>Material</b>	Tin-plated aluminum
<b>Number Of Openings</b>	6
<b>Number Of Circuits</b>	5
<b>Mounting Hole Position</b>	3
<b>Conductor Size</b>	14-4 AWG stranded copper, 14-8 AWG solid copper, 8-4 AWG stranded aluminum and 12-8 AWG solid aluminum
<b>Conductor Material</b>	Copper or aluminum
<b>Tightening Torque</b>	14-8 AWG 20 in-lb copper or aluminum and 6-4 AWG 31 in-lb copper or aluminum
<b>Dual Rating</b>	AL9CU
<b>Application</b>	Neutral and grounding

## Agency Approvals

<b>UL Listed File #</b>	E73393
<b>UL Recognized File #</b>	E12822
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/NA-403-1.pdf>  
See store item page for other formats.