

NA-418-1 Cut Sheet



Penn-Union neutral bar, tin-plated aluminum, 5 openings, 3 circuits, mounting hole position 2 and 4, copper or aluminum, AL9CU.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NA-418-1>

Technical Specifications

Brand	Penn-Union
Item	Neutral bar
Material	Tin-plated aluminum
Number Of Openings	5
Number Of Circuits	3
Mounting Hole Position	2 and 4
Conductor Size	14-2/0 AWG stranded copper, 14-8 AWG solid copper, 8-2/0 AWG stranded aluminum and 12-8 AWG solid aluminum

Conductor Material	Copper or aluminum
Tightening Torque	14-10 AWG 35 in-lb copper or aluminum, 8-2/0 AWG 120 in-lb copper, 8 AWG 50 in-lb aluminum and 6-2/0 AWG 120 in-lb aluminum
Dual Rating	AL9CU
Application	Neutral and grounding

Agency Approvals

UL Listed File #	E73393
UL Recognized File #	E12822
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/NA-418-1.pdf>
See store item page for other formats.