

# NC-420-1 Cut Sheet



Penn-Union neutral bar, copper, 6 openings, 4 circuits, mounting hole position 1 and 6, copper.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NC-420-1>

## Technical Specifications

|                               |   |
|-------------------------------|---|
| <b>Brand</b>                  | Penn-Union  |
| <b>Item</b>                   | Neutral bar   |
| <b>Material</b>               | Copper  |
| <b>Number Of Openings</b>     | 6   |
| <b>Number Of Circuits</b>     | 4   |
| <b>Mounting Hole Position</b> | 1 and 6   |
| <b>Conductor Size</b>         | 14-4 AWG stranded copper<br>and 14-8 AWG solid copper   |
| <b>Conductor Material</b>     | Copper  |
| <b>Tightening Torque</b>      | 14-8 AWG 20 in-lb copper<br>and 6-4 AWG 31 in-lb copper |
| <b>Application</b>            | Neutral and grounding                                   |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E73393   |
| <b>UL Recognized File #</b> | E12822   |
| <b>UL Hazardous File #</b>  | None   |
| <b>CSA File #</b>           | None   |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions -<br>No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                                 |
| <b>Other</b>                | <a href="#">RoHS Statement</a>   |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/NC-420-1.pdf>  
See store item page for other formats.