

NFLT-010-L40 Cut Sheet



ProSense hydrostatic submersible level transmitter, 0 to 10 psig (23.1ft of water column) sensing range, 4-20 mA, 1.26in diameter housing, shielded and vented 40ft cable, hazardous location rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NFLT-010-L40>

Technical Specifications

Brand	ProSense
Item	Submersible level transmitter
Sensor Type	Hydrostatic
Sensing Range	0 to 10 psig (23.1ft of water column)
Output	4-20 mA
Operating Voltage	11-30 VDC
Housing Size	1.26in diameter
Housing Material	Stainless steel
Electrical Connection	Shielded and vented 40ft cable
Jacket Material	Polyethylene
Application	Hazardous location rated

Agency Approvals

UL Listed File #	E537209
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/NFLT-010-L40.pdf>
See store item page for other formats.